

The background of the advertisement features a light-colored wood-grain surface on the left and several overlapping rolls of carpet on the right. The carpet rolls are in various colors: a large yellow roll at the top right, a dark blue roll below it, a teal roll below that, and a beige/multi-colored roll at the bottom left. The rolls are arranged in a way that they appear to be coming off a roll, creating a sense of depth and texture.

Crypton® Toolkit

DESIGNTEX

**Solutions for every space that
stand up to the toughest stains**

High Abrasion
Stain Resistant Finish
Fluid Barrier Backing
Disinfectant Treatable
Low VOC
No Antimicrobials
No DMF
No Flame Retardants
No PFAS
No Phthalates
No PVC
Healthier Hospitals
HPD
LEED
No Prop 65 Warning
REACH
UL GREENGUARD Gold
WELL

worden.




Mexico City Crypton® Frost
3107-803



Helsinki Crypton® Sand
3105-102



Sapporo Crypton® Stone
3103-104



Mexico City Crypton® Pewter
3107-801




Mexico City Crypton® Linen
3107-101



Barcelona Crypton® Hemp
3108-102




Helsinki Crypton® Latte
3105-103




Mexico City Crypton® Pebble
3107-103




Lake Placid Crypton® Granite
3106-102




Barcelona Crypton® Chamois
3108-201




Helsinki Crypton® Dijon
3105-201



Mexico City Crypton® Paprika
3107-701




Barcelona Crypton® Luggage
3108-701



Helsinki Crypton® Sienna
3105-701




Barcelona Crypton® Sienna
3108-702




Sapporo Crypton® Poppy
3103-301



Lake Placid Crypton® Brick
3106-701



Barcelona Crypton® Rosewood
3108-301



Sapporo Crypton® Crimson
3103-302



Helsinki Crypton® Otter
3105-104



Lake Placid Crypton® Multi
3106-901




Barcelona Crypton® Mist
3108-801




Barcelona Crypton® Fog
3108-802



Helsinki Crypton® Eucalyptus
3105-502




Sapporo Crypton® Meadow
3103-502




Barcelona Crypton® Aegean
3108-501



Barcelona Crypton® Linen
3108-103




Mexico City Crypton® Verde
3107-501




Barcelona Crypton® Blue
3108-401




Lake Placid Crypton® Opal
3106-101



Mexico City Crypton® Denim
3107-401



Sapporo Crypton® Indigo
3103-402



Mexico City Crypton® Graphite
3107-802




Sapporo Crypton® Indigo
3103-402




Sapporo Crypton® Denim
3103-401



Sapporo Crypton® Charcoal
3103-801




Helsinki Crypton® Teal
3105-503



Barcelona Crypton® Mystic
3108-402



Helsinki Crypton® Slate
3105-803



Helsinki Crypton® Denim
3105-401




Barcelona Crypton® Midnight
3108-403



Helsinki Crypton® Charcoal
3105-804



Helsinki Crypton® Midnight
3105-402



Lake Placid Crypton® Lapis
3106-401

Style Name	Style #	Content	Finish	Backing	Cleaning Code	Width	Repeat	Abrasion
Barcelona Crypton®	3108	100% Polyester	Crypton® (without PFAS or Antimicrobials)	Fluid Barrier (Crypton®)	WM Bleach (10:1)	54 inches (137 cm)	None	100,000 Wyzenbeek double rubs
Helsinki Crypton®	3105	100% Polyester	Crypton® (without PFAS or Antimicrobials)	Fluid Barrier (Crypton®)	WM Bleach (10:1)	54 inches (137 cm)	None	100,000 Wyzenbeek double rubs
Lake Placid Crypton®	3106	100% Polyester	Crypton® (without PFAS or Antimicrobials)	Fluid Barrier (Crypton®)	WM Bleach (10:1)	54 inches (137 cm)	None	100,000 Wyzenbeek double rubs
Mexico City Crypton®	3107	99% Polyester, 1% Linen	Crypton® (without PFAS or Antimicrobials)	Fluid Barrier (Crypton®)	WM	54 inches (137 cm)	None	100,000 Wyzenbeek double rubs
Sapporo Crypton®	3103	94% Polyester, 6% Linen	Crypton® (without PFAS or Antimicrobials)	Fluid Barrier (Crypton®)	WM	54 inches (137 cm)	None	100,000 Wyzenbeek double rubs

Meets or exceeds these ACT® performance standards:



Additional colorways available
For samples please call 800.221.1540

Cleaning Codes

Bleach Treatable with a 4:1 or 10:1 water-to-bleach dilution for the lifetime of the product.
WM Clean only with water-based detergents or mild solvent-based cleaners using the minimum amount of liquid. Do not use harsh solvents.

Bleach and Disinfectant Testing

All products have been tested with bleach (sodium hypochlorite) and/or a variety of disinfectants (alcohol, hydrogen peroxide, quaternary ammonium). Scan the QR code below for specific test results.

Flammability

All textiles comply with California TB 117-2013.

Abrasion

Abrasion has been tested with the Wyzenbeek method using either cotton duck (CD) or wire screen (WS) as the abradant, or the Martindale method using worsted wool as the abradant. ACT guidelines require at least 30,000 Wyzenbeek double rubs or 40,000 Martindale cycles for woven upholsteries, or 50,000 Wyzenbeek double rubs for coated upholsteries in heavy duty single-shift application. Multiple factors affect fabric durability and appearance retention, including end-user application and proper maintenance. Abrasion test results exceeding ACT Performance Guidelines are not an indicator of product lifespan.

worden.

www.wordencompany.com

© 2026 Worden Company

Learn more

